

Tools

List of tools

| Tool Name | | Model | Applicable Connectors |
|------------------------------------|----------------------------|-------------|---|
| Tools for lever operation | | XN2Z-0001 | XN2A, XN2B |
| Screwdriver | For terminal pitch 2.54 mm | XW4Z-00A | XW4H, XW4L (terminal pitch 2.54 mm) |
| | For terminal pitch 3.81 mm | XW4Z-00B | XW4 (terminal pitch 3.81 mm) |
| | For terminal pitch 5.08 mm | XW4Z-00C | XW4 (terminal pitch 5.08 mm) |
| Press-fit tool | | XY2B-0002 | XG4M, XG4E, XG2A, XC6D, XC6H |
| Attachment | | XY2B-1004 | XG4E |
| | | XY2B-1006 | XG2A |
| | | XY2B-1007 | XG4M |
| Spacer | | XY2B-1401 | XG4E 10, 14 contacts |
| | | XY2B-1402 | XG4E 16, 20 contacts |
| | | XY2B-1403 | XG4E 26, 30 contacts |
| | | XY2B-1404 | XG4E 34 contacts |
| | | XY2B-1405 | XG4E 40 contacts |
| | | XY2B-1406 | XG4E 50 contacts |
| | | XY2B-1407 | XG4E 60, 64 contacts |
| Simple wire IDC tool set | | XY2B-2104-N | XG5M |
| | | XY2B-2105-N | XC6V |
| Simple IDC tool | | XY2B-7006 | XG5M |
| Manual crimping tool | | XY2B-7007 | XG5N |
| IC removal tool | | XY2C-0101 | XR2A/B/T 14, 16, 18, 20 contacts |
| | | XY2C-0103 | XR2A/B/T 24, 28, 32, 40 contacts |
| Coding cutter | | XY2D-0001 | XC5 |
| Special simple press-fit tool | | XY2D-1004 | XC8B, XC8D, XC8F, XC8L, each L-shaped socket |
| Press-fit tool | | XY2D-1005 | XC5, XC8, press-fits |
| Contact repair tools for plugs | | XY2D-1006 | XC5E double rows, 64 contacts press-fit |
| | | XY2D-1007 | XC5E double rows, 32 contacts press-fit |
| | | XY2D-1008 | XC5G triple rows, 96 (64) contacts press-fit |
| | | XY2D-1009 | XC5G triple rows, 48 contacts press-fit |
| Contact repair tools for sockets | | XY2D-1010 | XC5B double rows, 64 contacts press-fit |
| | | XY2D-1011 | XC5B double rows, 32 contacts press-fit |
| | | XY2D-1012 | XC5D triple rows, 96 (64) contacts press-fit |
| | | XY2D-1013 | XC5D triple rows, 48 contacts press-fit |
| Support blocks | | XY2D-1014 | XC5B/E double rows, 64 contacts press-fit |
| | | XY2D-1015 | XC5D/G triple rows, 96 (64) contacts press-fit |
| Plungers | | XY2D-1017 | XC5 press-fit |
| Contact repair tool holder (upper) | | XY2D-3001 | XC8 (required to use XY2D-1005) |
| Contact repair tool holder (lower) | | XY2D-3002 | XC8 (required to use XY2D-1005) |
| Contact repair tool (upper) | | XY2D-3003 | XC8B-1101L, XC8B-1101L-NN, XC8D-1251L-SN, XC8D-1251L-NN, XC8L-1251L-SN |
| Contact repair tool (lower) | | XY2D-3004 | XC8B-1101L, XC8B-1101L-NN, XC8D-1251L-SN, XC8D-1251L-NN, XC8L-1251L-SN |
| Contact repair tool (upper) | | XY2D-3005 | XC8D-0951L, XC8D-0951L-NN |
| Contact repair tool (lower) | | XY2D-3006 | XC8D-0951L, XC8D-0951L-NN |
| Contact repair tool (upper) | | XY2D-3007 | XC8D-1101L, XC8D-1101L-NN |
| Contact repair tool (lower) | | XY2D-3008 | XC8D-1101L, XC8D-1101L-NN |
| Contact repair tool (upper) | | XY2D-3009 | XC8F-0551L-SN, XC8F-0551L-NN |
| Contact repair tool (lower) | | XY2D-3010 | XC8F-0551L-SN, XC8F-0551L-NN |
| Contact repair tool (upper) | | XY2D-3011 | XC8A-1101S-0, XC8A-1101S-4, XC8A-1101S-ACP, XC8A-1101S-AWP |
| Contact repair tool (lower) | | XY2D-3012 | XC8A-1101S-0, XC8A-1101S-4, XC8A-1101S-ACP, XC8A-1101S-AWP, XC8C-1251S-AC, XC8C-1251S-AW, XC8K-1251S-AC |
| Contact repair tool (upper) | | XY2D-3013 | XC8C-0951S-0, XC8C-0951S-4 |
| Contact repair tool (lower) | | XY2D-3014 | XC8C-0951S-0, XC8C-0951S-4 |
| Contact repair tool (upper) | | XY2D-3015 | XC8C-1101S-0, XC8C-1101S-4, XC8C-1101S-AC, XC8C-1101S-AW |

Tools

| Tool Name | Model | Applicable Connectors |
|-----------------------------|-----------|--|
| Contact repair tool (lower) | XY2D-3016 | XC8C-1101S-0, XC8C-1101S-4, XC8C-1101S-AC, XC8C-1101S-AW |
| Contact repair tool (upper) | XY2D-3017 | XC8C-1251S-AC, XC8C-1251S-AW |
| Contact repair tool (upper) | XY2D-3018 | XC8E-0551S-ACP, XC8E-0551S-AWP |
| Contact repair tool (lower) | XY2D-3019 | XC8E-0551S-ACP, XC8E-0551S-AWP |
| Contact repair tool (upper) | XY2D-3020 | XC8K-1251S-AC |
| 20 dia. ring | XY2D-3024 | XC8 (required to use XY2D-1005) |
| Centering plate (left) | XY2D-3025 | XC8 (required to use XY2D-3001 or XY2D-3002) |
| Centering plate (right) | XY2D-3026 | XC8 (required to use XY2D-3001 or XY2D-3002) |
| Spacer block (5mm) | XY2D-3027 | XC8 (required to use XY2D-3001 or XY2D-3002) |
| Spacer block (25mm) | XY2D-3028 | XC8 (required to use XY2D-3001 or XY2D-3002) |
| Spacer block (38mm) | XY2D-3029 | XC8 (required to use XY2D-3001 or XY2D-3002) |
| Block for press-fitting | XY2D-3030 | XC8A-1100, XC8A-1101, XC8A-1102 |
| | XY2D-3031 | XC8C-0950, XC8C-0951, XC8C-0952 |
| | XY2D-3032 | XC8C-1100, XC8A-1101, XC8C-1102 |
| Contact removal tool | XY2E-0001 | XG5M |
| Contact cutting driver | XY2E-0002 | XC4A, XG4C, XG4E |
| Contact removal tool | XY2E-0003 | XG5N |

Please check each region's Terms & Conditions by region website.

OMRON Corporation
Electronic and Mechanical Components Company

Regional Contact

Americas

<https://www.components.omron.com/>

Asia-Pacific

<https://ecb.omron.com.sg/>

Korea

<https://www.omron-ecb.co.kr/>

Europe

<http://components.omron.eu/>

China

<https://www.ecb.omron.com.cn/>

Japan

<https://www.omron.co.jp/ecb/>