


G3VM-31QR/61QR2/101QR1

MOS FET Relays S-VSON(L) 4Pin, High-current and Low-ON-resistance Type

Compact S-VSON(L) Package MOS FET Relays with High Capacity Switching

- A compact L2.0 × W1.45 × H1.3 mm S-VSON(L) package helps to reduce the space required by circuit boards.
- Weighs just 0.01 g per item, helping to reduce the weight of the circuit boards.
- Load voltage 30 V/60 V/100 V.
30-V Relay: Continuous load current of 1.5 A max.
60-V Relay: Continuous load current of 1.0 A max.
100-V Relay: Continuous load current of 0.65 A max.
- High Ambient operating temperature: -40°C to +110°C



Note: The actual product is marked differently from the image shown here.


* As of March 2018 Survey by OMRON.

Application Examples

- Semiconductor test equipment
- Test & measurement equipment
- Communication equipment
- Data loggers

Package (Unit : mm, Average)

S-VSON(L) 4Pin



Note: The actual product is marked differently from the image shown here.

Model Number Legend

G3VM-□□□□□
1 2 3 4 5

1. Load Voltage

3: 30 V
6: 60 V
10: 100 V

2. Contact form Package type

1: 1a (SPST-NO)

3. Package type

Q: S-VSON(L) 4Pin

5. Other information

When specifications overlap, serial code is added in the recorded order.

4. Additional functions

R: Low On-resistance

Ordering Information

Package type	Contact form	Terminals	Load voltage (peak value) *	Continuous load current (peak value) *	Packing/Tape cut		Packing/Tape & reel	
					Model	Minimum package quantity	Model	Minimum package quantity
S-VSON(L) 4	1a (SPST-NO)	Surface-mounting Terminals	30 V	1,500 mA	G3VM-31QR	1 pc.	G3VM-31QR (TR05)	500 pcs.
			60 V	1,000 mA	G3VM-61QR2		G3VM-61QR2 (TR05)	
			100 V	650 mA	G3VM-101QR1		G3VM-101QR1 (TR05)	

* The AC peak and DC value are given for the load voltage and continuous load current.

Note: Taping cut products are packaged without humidity resistance. Use manual soldering to mount them.

G3VM-31QR/61QR2/101QR1

S-VSON

■ Absolute Maximum Ratings (Ta = 25°C)



Item		Symbol	G3VM-31QR		G3VM-61QR2	G3VM-101QR1	Unit	Measurement conditions
Input	LED forward current	I _F	30				mA	Ta≥25°C
	LED forward current reduction rate	ΔI _F /°C	−0.3				mA/°C	
	LED reverse voltage	V _R	5				V	
	Connection temperature	T _J	125				°C	
Output	Load voltage (AC peak/DC)	V _{OFF}	30	60	100		V	Ta≥25°C
	Continuous load current (AC peak/DC)	I _o	1500	1000	650		mA	
	ON current reduction rate	ΔI _o /°C	−15	−10	−6.5		mA/°C	
	Pulse ON current	I _{op}	4.5	3	2		A	t=100 ms, Duty=1/10
	Connection temperature	T _J	125				°C	
	Dielectric strength between I/O *	V _{I-O}	500				V _{rms}	AC for 1 min
	Ambient operating temperature	T _a	−40 to +110				°C	With no icing or condensation
	Ambient storage temperature	T _{stg}	−40 to +125				°C	
Soldering temperature		—	260				°C	10 s

* The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.

■ Electrical Characteristics (Ta = 25°C)

Item		Symbol		G3VM-31QR	G3VM-61QR2	G3VM-101QR1	Unit	Measurement conditions
Input	LED forward voltage	V _F	Minimum	1.1			V	I _F =10 mA
			Typical	1.21				
			Maximum	1.4				
	Reverse current	I _R	Maximum	10			μA	V _R =5 V
	Capacity between terminals	C _T	Typical	30			pF	V=0, f=1 MHz
	Trigger LED forward current	I _{FT}	Typical	0.6	0.7		mA	I _o =100 mA
			Maximum	3				
Release LED forward current	I _{FC}	Minimum	0.1			mA	I _{OFF} =10 μA	
Output	Maximum resistance with output ON	R _{ON}	Typical	0.1	0.2	0.4	Ω	G3VM-31QR/61QR2, I _o =1000 mA, I _F =5 mA, t<1 s G3VM-101QR1, I _o =650 mA, I _F =5 mA, t<1 s
			Maximum	0.2	0.3	0.6		
	Current leakage when the relay is open	I _{LEAK}	Maximum	1	1000 (1)		nA	G3VM-31QR :V _{OFF} = 20 V G3VM-61QR2 :V _{OFF} = 60 V (V _{OFF} =50 V) G3VM-101QR1 :V _{OFF} = 100 V (V _{OFF} =80 V)
	Capacity between terminals	C _{off}	Typical	120	80	50	pF	V=0, f=100 MHz, t<1 s
			Maximum	—	150	—		
	Capacity between I/O terminals		C _{I-O}	Typical	1	0.9		pF
Insulation resistance between I/O terminals		R _{I-O}	Typical	10 ⁸			MΩ	V _{I-O} =500 VDC, R _{oH} ≤60%
Turn-ON time		t _{ON}	Typical	0.8	0.75	0.6	ms	I _F =5 mA, R _L =200 Ω, V _{DD} =20 V *
			Maximum	2				
Turn-OFF time		t _{OFF}	Typical	0.05	0.04		ms	
			Maximum	1	0.3			

* Turn-ON and Turn-OFF Times



■ Recommended Operating Conditions


For usage with high reliability, Recommended Operation Conditions is a measure that takes into account the derating of Absolute Maximum Ratings and Electrical Characteristics.

Each item on this list is an independent condition, so it is not simultaneously satisfy several conditions.


Item	Symbol		G3VM-31QR	G3VM-61QR2	G3VM-101QR1	Unit
Load voltage (AC peak/DC)	V _{DD}	Maximum	24	48	80	V
Operating LED forward current	I _F	Minimum	5			mA
		Typical	7.5			
		Maximum	20			
Continuous load current (AC peak/DC)	I _O	Maximum	1300	1000	650	
Ambient operating temperature	T _a	Minimum	−20			°C
		Maximum	100			

Engineering Data


LED forward current vs. Ambient temperature




Continuous load current vs. Ambient temperature




LED forward current vs. LED forward voltage




Continuous load current vs. On-state voltage




On-state resistance vs. Ambient temperature




Trigger LED forward current vs. Ambient temperature




Turn ON, Turn OFF time vs. LED forward current




Turn ON, Turn OFF time vs. Ambient temperature




Current leakage vs. Load voltage



Current leakage vs. Ambient temperature




Output terminal capacitance vs. Load voltage



■ Appearance / Terminal Arrangement / Internal Connections

■ Appearance


S-VSON (Super-Very Small Outline Non-leaded)
S-VSON(L) 4Pin



* Actual model name marking for each model

Model	Marking
G3VM-31QR	3Q0
G3VM-61QR2	6Q2
G3VM-101QR1	AQ1

■ Terminal Arrangement/Internal Connections (Top View)



- Note** 1. The actual product is marked differently from the image shown here.
2. "G3VM" does not appear in the model number on the Relay.

■ Dimensions



CAD Data marked products, 2D drawings and 3D CAD models are available.
For CAD information, please visit our website, which is noted on the last page.

(Unit: mm)

S-VSON(L) 4Pin


Surface-mounting Terminals

Weight: 0.01 g



Actual Mounting Pad Dimensions

(Recommended Value, Top View)



Note: Unless otherwise specified, the dimensional tolerance is ± 0.1 mm.

CAD Data

■ Safety Precautions

- Refer to "Common Precautions" for all G3VM models.

Please check each region's Terms & Conditions by region website.

OMRON Corporation

Device & Module Solutions Company

Regional Contact

Americas

<https://components.omron.com/us>

Asia-Pacific

<https://components.omron.com/ap>

Korea

<https://components.omron.com/kr>

Europe

<https://components.omron.com/eu>

China

<https://components.omron.com.cn>

Japan

<https://components.omron.com/jp>