


G3VM-31QV□/61QV□□

MOS FET Relays S-VSON(L), Voltage Driven Type

World's smallest * class S-VSON(L) package with voltage drive MOS FET relay with current limiting internal resistor on the input side

* As of January 2020 Survey by OMRON.

- Operating input forward voltage: H/Recommendation 5 V(Typical), L/Recommendation 2.5 V(Typical)
- Load voltage: 30 V/60 V
 - G3VM-31QVH/L: Continuous Load current of 1.5 A max.
 - G3VM-61QV2H/L: Continuous Load current of 1.0 A max.
 - G3VM-61QVH: Continuous Load current of 0.4 A max.
- High Ambient operating temperature: -40°C to +110°C




Note: The actual product is marked differently from the image shown here.

Application Examples

- Semiconductor test equipment
- Communication equipment
- Test & measurement equipment
- Data loggers

Package (Unit : mm, Average)

S-VSON(L)4 pin



Note: The actual product is marked differently from the image shown here.

Model Number Legend

G3VM-□□□□□□
1 2 3 4 5 6

1. Load Voltage

- 3: 30 V
- 6: 60 V

2. Contact form

- 1: 1a (SPST-NO)

3. Package

- Q: S-VSON(L)4-pin

4. Additional functions

- V: Voltage Driven Type

5. Serial code

- When specifications overlap, serial code is added in the recorded order.

6. Input forward voltage

- H: High voltage
- L: Low voltage

Ordering Information

| Package | Contact form | Terminals | Load voltage (peak value) * | Continuous load current (peak value) * | Tape cut packaging | | Tape packaging | |
|------------|--------------|----------------------------|-----------------------------|--|--------------------|--------------------------|-------------------|--------------------------|
| | | | | | Model | Minimum package quantity | Model | Minimum package quantity |
| S-VSON(L)4 | 1a (SPST-NO) | surface-mounting Terminals | 30 V | 1,500 mA | G3VM-31QVH | 1 pc. | G3VM-31QVH(TR05) | 500 pcs. |
| | | | | | G3VM-31QVL | | G3VM-31QVL(TR05) | |
| | | | 60 V | 1,000 mA | G3VM-61QV2H | | G3VM-61QV2H(TR05) | |
| | | | | | G3VM-61QV2L | | G3VM-61QV2L(TR05) | |
| | 400 mA | G3VM-61QVH | G3VM-61QVH(TR05) | | | | | |

Note: To order tape packaging for Relays with surface-mounting terminals, add "(TR05)" to the end of the model number. Tape-cut S-VSON(L)s are packaged without humidity resistance. Use manual soldering to mount them. Refer to common precautions.

* The AC peak and DC value are given for the load voltage and continuous load current.

G3VM-31QV□/61QV□□

Absolute Maximum Ratings (Ta = 25°C)


| Item | | Symbol | G3VM-31QVH | G3VM-31QVL | G3VM-61QV2H | G3VM-61QV2L | G3VM-61QVH | Unit | Measurement conditions |
|-------------------------------|--------------------------------------|---------------------|------------|------------|-------------|-------------|------------|-------------------------------|-------------------------|
| Input | Input forward voltage | V _{IN} | 6 | 3 | 6 | 3 | 6 | V | |
| | Input reverse voltage | V _{RIN} | 6 | | | | | V | |
| | Connection temperature | T _J | 125 | | | | | °C | |
| Output | Load voltage (AC peak/DC) | V _{OFF} | 30 | | 60 | | | V | |
| | Continuous load current (AC peak/DC) | I _o | 1500 | | 1000 | | 400 | mA | |
| | ON current reduction rate | ΔI _o /°C | -15 | | -10 | | -4 | mA/°C | Ta ≥ 25°C |
| | Pulse ON current | I _{op} | 4500 | | 3000 | | 1200 | mA | t = 100 ms, Duty = 1/10 |
| | Connection temperature | T _J | 125 | | | | | °C | |
| | Dielectric strength between I/O * | V _{I-O} | 500 | | | | | V _{rms} | AC for 1 min |
| Ambient operating temperature | T _a | -40 to +110 | | | | | °C | With no icing or condensation | |
| Ambient storage temperature | T _{stg} | -40 to +125 | | | | | °C | | |
| Soldering temperature | - | 260 | | | | | °C | 10 s | |

* The dielectric strength between the input and output was checked by applying voltage between all pins on the LED side and all pins on the light-receiving side.

Electrical Characteristics (Ta = 25°C)

| Item | | Symbol | G3VM-31QVH | G3VM-31QVL | G3VM-61QV2H | G3VM-61QV2L | G3VM-61QVH | Unit | Measurement conditions | |
|---|--|-------------------|-----------------|------------|-------------|-------------|------------|------|--|--|
| Input | Reverse current | I _r | Maximum | | | | | 10 | μA | V _R = 5 V |
| | Capacity between terminals | C _T | Typical | | | | | 30 | pF | V = 0, f = 1 MHz |
| | Input forward current | I _F | Typical | 6.3 | 14.3 | 6.3 | 14.3 | 6.2 | mA | V _{IN} = 5 V (G3VM-31QVH/-61QVH/-61QV2H), V _{IN} = 2.5 V (G3VM-31QVL/-61QV2L) |
| | Operate voltage | V _{FON} | Typical | 1.4 | 1.2 | 1.4 | 1.2 | 1.5 | V | I _o = 100 mA |
| | | | Maximum | 3 | 1.6 | 3 | 1.6 | 3 | | |
| Release voltage | V _{FOFF} | Minimum | 0.8 | | | | | V | I _{OFF} = 10 μA | |
| | | Typical | 1.4 | 1.2 | 1.4 | 1.1 | 1.5 | | | |
| Output | Maximum resistance with output ON | R _{ON} | Typical | 0.1 | | 0.2 | | 1 | Ω | I _o = Continuous load current ratings, t < 1 s, V _{IN} = 5 V (G3VM-31QVH/-61QVH/-61QV2H), V _{IN} = 2 V (G3VM-31QVL/-61QV2L) |
| | | | Maximum | 0.2 | | 0.3 | | 1.5 | | |
| | Current leakage when the relay is open | I _{LEAK} | Maximum | 1 | | | | | nA | V _{OFF} = 20 V (G3VM-31QVH/L), V _{OFF} = 50 V (G3VM-61QVH, -61QV2H/L) |
| Capacity between terminals | C _{off} | Typical | 120 | | 80 | | - | pF | V = 0, f = 1 MHz, t < 1 s | |
| | | Maximum | 150 | | | | 20 | | | |
| Capacity between I/O terminals | C _{I-O} | Typical | 1 | | | | | pF | V _s = 0 V, f = 1 MHz | |
| Insulation resistance between I/O terminals | R _{I-O} | Minimum | 1000 | | | | | MΩ | V _{I-O} = 500 VDC, R _{oH} ≤ 60% | |
| | | Typical | 10 ⁸ | | | | | | | |
| Turn-ON time | t _{ON} | Maximum | 2.0 | | | 1.0 | 0.5 | ms | V _{DD} = 20 V, R _L = 200 Ω V _{IN} = 5 V (G3VM-31QVH/-61QVH/-61QV2H), V _{IN} = 2 V (G3VM-31QVL/-61QV2L) | |
| Turn-OFF time | t _{OFF} | Maximum | 0.2 | | | | | | | |

* Turn-ON and Turn-OFF Times



Recommended Operating Conditions

To ensure highest reliability, Recommended Operation Conditions is a measure that takes into account the derating of Absolute Maximum Ratings and Electrical Characteristics.


Each item on this list is an independent condition, so it is not simultaneously satisfy several conditions.

| Item | Symbol | G3VM-31QVH | G3VM-31QVL | G3VM-61QV2H | G3VM-61QV2L | G3VM-61QVH | Unit | |
|--------------------------------------|-----------------|------------|------------|-------------|-------------|------------|------|----|
| Load voltage (AC peak/DC) | V _{DD} | Maximum | 24 | | | 48 | | V |
| Operating input forward voltage | V _{IN} | Minimum | 4 | 2 | 4 | 2 | 4 | V |
| | | Typical | 5 | 2.5 | 5 | 2.5 | 5 | |
| | | Maximum | 6 | 3 | 6 | 3 | 6 | |
| Continuous load current (AC peak/DC) | I _o | Maximum | 1500 | | 1000 | | 400 | mA |
| Ambient operating temperature | T _a | Minimum | -20 | | | | | °C |
| | | Maximum | 100 | | | | | |

Engineering Data


Continuous load current vs. Ambient temperature

G3VM-31QVH/31QVL/61QVH/61QV2H/61QV2L




Continuous load current vs. On-state voltage

G3VM-31QVH/31QVL/61QVH/61QV2H/61QV2L




On-state resistance vs. Ambient temperature

G3VM-31QVH/31QVL/61QVH/61QV2H/61QV2L




Operate voltage vs. Ambient temperature

G3VM-31QVH/31QVL/61QVH/61QV2H/61QV2L




Turn ON, Turn OFF time vs. Input forward voltage

G3VM-31QVL/61QV2L




G3VM-31QVH/61QVH/61QV2H




Turn ON, Turn OFF time vs. Ambient temperature

G3VM-31QVL/61QV2L



G3VM-31QVH/61QVH/61QV2H




G3VM-31QV□/61QV□□


Engineering Data

Current leakage vs. Load voltage

G3VM-31QVH/31QVL/61QV2H/61QV2L




G3VM-61QVH




Current leakage vs. Ambient temperature

G3VM-31QVH/31QVL/61QV2H/61QV2L




G3VM-61QVH



Output terminal capacitance vs. Load voltage

G3VM-31QVH/31QVL/61QVH/61QV2H/61QV2L




■ Appearance / Terminal Arrangement / Internal Connections

● Appearance

S-VSON(L)
(Super-Very Small Outline Non-leaded)

S-VSON(L) 4-pin




* Actual model name marking for each model

| Model | Marking |
|-------------|---------|
| G3VM-31QVH | 3V1 |
| G3VM-31QVL | 3V0 |
| G3VM-61QV2H | 6V1 |
| G3VM-61QV2L | 6V0 |
| G3VM-61QVH | 6V2 |

Note: 1. The actual product is marked differently from the image shown here.

Note: 2. "G3VM" does not appear in the model number on the Relay.



● Terminal Arrangement/Internal Connections (Top View)



■ Dimensions (Unit: mm)


Surface-mounting Terminals

Weight: 0.01 g



Actual Mounting Pad Dimensions

(Recommended Value, Top View)



Unless otherwise specified, the dimensional tolerance is ± 0.1 mm.

Note: The actual product is marked differently from the image shown here.

■ Safety Precautions

- Refer to the *Common Precautions for All MOS FET Relays* for precautions that apply to all MOS FET Relays.

Please check each region's Terms & Conditions by region website.

OMRON Corporation

Device & Module Solutions Company

Regional Contact

Americas

<https://components.omron.com/us>

Asia-Pacific

<https://components.omron.com/ap>

Korea

<https://components.omron.com/kr>

Europe

<https://components.omron.com/eu>

China

<https://components.omron.com.cn>

Japan

<https://components.omron.com/jp>

© OMRON Corporation 2020-2022 All Rights Reserved.

In the interest of product improvement, specifications are subject to change without notice.

Cat. No. K319-E1-02

1122 (0220)