Ultra Subminiature Basic Switch

Compact, long-life surface-mount terminal type operation switches High load types are also available.

- High operating force type also achieving long durability (OF = 1.2 N, Durability: 10,000,000 operations. OF = 0.6 N, Durability: 20,000,000 operations.)
- Compact size 8.6 × 4.8 × 3.0 mm (W × D × H) contributing to down-sizing of module
- · Clear click feeling
- Embossed taping package for automatic mounting

Model Number Legend



(2) External shape 1: With boss

0: Without boss

1: 1.2±0.4 N {122±41 gf} 2: 0.6±0.2 N {61±20 gf}

(1) Operating Force (OF)

List of Models

| Operating Force (OF) | Durability, Mechanical/Electrical | With/Without boss | Button color | Cover color | Model | Minimum packing unit * |
|----------------------|-----------------------------------|--------------------------------------|--------------|---------------|---------------|------------------------|
| | 5,000,000 operations min. | With boss | | /HITE BLACK | D2LS-11 | |
| 1.2 N {122 gf} | | Without boss | WHITE | | D2LS-10 | |
| | 10,000,000 operations min. | With boss | | | D2LS-11 (10M) | 2,000 pcs. |
| 0.6 N {61 gf} | 5,000,000 operations min. | With boss | | BLACK | D2LS-21 | 2,000 pcs. |
| | 10,000,000 operations min. | With boss | boss BLUE | | D2LS-21 (10M) | |
| | 20,000,000 operations min. | 0,000 operations min. With boss BLUE | BLUE | D2LS-21 (20M) | | |

Contact Specifications

| | Specification | Crossbar | |
|-------------------------------------------|----------------------|------------|--|
| Contact | Material | Silver | |
| | Gap (standard value) | 0.4 mm | |
| Minimum applicable load (reference value) | | 5 VDC 1 mA | |


Ratings

| Rated voltage | Resistive load |
|---------------|----------------|
| 6 VDC | 1 mA |

Note: The rating values apply under the following test conditions. Ambient temperature: 20 $\pm\,2^\circ C$ Ambient humidity: 65 ± 5%RH Operating frequency: 300 operations/1 min.

Contact Form

SPST-NO



| Operating Force (OF) | Durability, Mechanical/Electrical | With/Without boss | Button color | Cover color | Model | Minimum packing unit * |
|----------------------|------------------------------------------|----------------------------------------------------------------------------------|---------------|-------------|---------------|------------------------|
| | 5,000,000 operations min. | With boss | | BLACK | D2LS-11 | |
| 1.2 N {122 gf} | | Without boss | WHITE | | D2LS-10 | |
| | 10,000,000 operations min. | With boss | | | D2LS-11 (10M) | 2,000,000 |
| | 5,000,000 operations min. | With boss GRAY With boss BLACK With boss BLUE GRAY | BLACK | D2LS-21 | 2,000 pcs. | |
| 0.6 N {61 gf} | 10,000,000 operations min. | | BLUE | GRAY | D2LS-21 (10M) | |
| | 20,000,000 operations min. With boss BLU | BLUE | D2LS-21 (20M) | | | |

Characteristics

| | | D2LS-10 D2LS-11 D2LS-21 | D2LS-11 (10M) D2LS-21 (10M) | D2LS-21 (20M) | | |
|------------------------------------|------------------------------------|--------------------------------------------------------------|----------------------------------------------------|----------------------------------------------------|--|--|
| Operating speed | | 1 mm to 500 mm/s | 1 mm to 500 mm/s | | | |
| Operatiing frequency | Mechanical/Electrical | 300 operations/1 min. max. | | | | |
| Insulation resistance | | 100 MΩ min. (at 500 VDC) | | | | |
| Contact resistance (initial value) | | 100 mΩ max. | | | | |
| Dielectric strength | Between terminals of same polarity | 600 VAC 50/60 Hz 1 min | | | | |
| Vibration resistance *1 | Malfunction | 10 to 55 Hz, 1.5 mm double amplitude | | | | |
| Shock resistance *1 | Destruction | 1,000 m/s ² max. | | | | |
| | Malfunction | 300 m/s² max. | | | | |
| Durability *2 | Mechanical/Electrical | 5,000,000 operations min. (at 300 ops./1 min.) | 10,000,000 operations min. (at 300 ops./1 min.) | 20,000,000 operations min. (at 300 ops./1 min.) | | |
| Degree of protection | | Equivalent to IP40 | | | | |
| Ambient operating tamperature | | -25 to +85°C (at 60%RH Max.) (with no icing or condensation) | | | | |
| Ambient operation humidity | | 85%RH max. (for +5 to +35°C) | | | | |
| Weight | | Approx. 0.16 g | | | | |


Note: The data given above are initial values.
*1. The values are at Free Position and Total Travel Position values. Close or open circuit of the contact is 1ms max.
*2. For testing conditions, consult your OMRON sales representative.

4.8±0.15

2.7

J.


Dimensions (Unit: mm) / Operating Characteristics



| oporating onarabitorior | | D2LS-11 (10M) | D2LS-21 (20M) |
|------------------------------------|---------------|------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------|
| Operating Force Releasing Force | OF RF min. | $\begin{array}{c} 1.2 \pm 0.4 \ N \ \{122 \pm 41 \ gf\} \\ 0.15 \ N \ \{15 \ gf\} \end{array}$ | $\begin{array}{c} 0.6\pm 0.2 \text{ N} \ \{61\pm 20 \text{ gf}\} \\ 0.15 \text{ N} \ \{15 \text{ gf}\} \end{array}$ |
| Overtravel | OT min. | 0.1 mm | |
| Movement Differential | MD max. | 0.12 mm | |
| Operating Position | OP | $3.2 \pm 0.2 \text{ mm}$ | |
| Free Position | FP | $3.5 \pm 0.2 \text{ mm}$ | |

Note:Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.

Packaging Specifications (Unit: mm)



Precautions

★ Refer to General Information.

Cautions

Use the Switch within the rated voltage and current ranges, otherwise the Switch may have a shortened durability, radiate heat, or burn out. This particularly applies to the instantaneous voltages and currents when switching.

Correct Use

Soldering

General Precautions


Before soldering the Switch on a multilayer PCB, test to confirm that soldering can be performed properly. Otherwise the Switch may be deformed by the soldering heat on the pattern or lands of the multilayer PCB.

Do not solder the Switch more than twice, including rectification soldering. An interval of five minutes is required between the first and the second soldering.

• Reflow Soldering (Surface Mounting)

Solder the terminals within the heating curve shown in the following diagram.

The peak temperature may vary depending on the reflow bath used. Confirm the conditions beforehand.



Manual Soldering

Soldering temperature: 350°C max. at the tip of the soldering iron

Soldering time: 3 s max.

Washing

The Switch is not sealed, and cannot be washed. Doing so will cause the washing agent, together with flux or dust particles on the PCB, to enter the Switch, resulting in malfunction.

Application Environment

Do not use the Switch in locations that are subject to toxic gas, silicon, excessive dust, excessive dirt, high temperatures, high humidity, sudden temperature changes, water splashes, or oil splashes.

Otherwise, damage resulting by faulty contact of the Switch contacts, corrosion, or other causes, or other functional faults may occur.

Please check each region's Terms & Conditions by region website.

OMRON Corporation Device & Module Solutions Company

Regional Contact Americas https://components.omron.com/us Asia-Pacific https://components.omron.com/ap Korea https://components.omron.com/kr

Europe https://components.omron.com/eu China https://components.omron.com.cn Japan https://components.omron.com/jp

© OMRON Corporation 2013-2023 All Rights Reserved.

In the interest of product improvement, specifications are subject to change without notice.

Cat. No. B122-E1-04 0823 (1213)