

DIN Twin-contact Connectors

XC5

A Wide Variety of DIN Connectors That Conform to UL/CSA Standards.

- Fully preserve the characteristics of normal DIN connectors while increasing the number of terminals available.
- A wide product range to fit almost any application.
- Meeting world market needs with products ranging from one-piece connectors (card edge) to two-piece connectors.
- Use the twin-contact system for high reliability.
- Lower insertion force as a result of FEM analysis techniques.



■Ratings and Characteristics


Rated current	2 A
Rated voltage	300 VAC
Contact resistance	20 m Ω max. (at 20 mV, 100 mA max.)
Insulation resistance	10^6 M Ω min. (at 100 VDC)
Dielectric strength	1,000 VAC for 1 min (leakage current: 1 mA max.)
Total insertion force	0.59 N max. per contact
Removal force	0.15 N min. (with test gauge, t = 0.56 mm)
Insertion durability	200 times
Ambient operating temperature	−55 to 125°C (with no icing at low temperature)


■Materials and Finish

Item		Plugs	Sockets	
Housings		Fiber-glass reinforced PBT resin (UL94 V-0)/gra		
Contacts	Mating end	Brass/nickel base, 0.4-μm gold plating (See note 1.)	Phosphor bronze/nickel base, 0.4-µm gold plating (See note 1.)	
	Terminal Brass/ni 2.0-μm i		Phosphor bronze/nickel base, 2.0-μm tin plating	

: 1. For non-standard plating specifications, contact your OMRON representative

XC5A Double-row Plugs, DIN B-type (Standard)






XC5A
DIP terminal cross-section view

Mounting holes (bottom view)





Dimensions

No. of			Dimensi	ons (mm)		Coding Key positions
contacts	Α	В	С	D	Е	F	(contact No.)
20	37.9	32.1	22.86	33.02	28.1	29.3	3, 8
32	53.2	47.4	38.10	48.26	43.3	44.6	5, 12
44	68.4	62.6	53.34	63.50	58.5	59.8	4, 9, 14, 19
50	76.0	70.2	60.96	71.12	66.2	67.4	5, 10, 16, 21
64	93.8	88.0	78.74	88.90	83.9	85.2	6, 13, 20, 27
100	139.5	133.7	124.46	134.62	129.7	130.9	10, 20, 31, 41

No. of contacts	Terminal type	Model
20*		XC5A-2022
32		XC5A-3222
44*	Right-angle DIP	XC5A-4422
50*	terminals	XC5A-5022
64		XC5A-6422
100*		XC5A-0122

^{*}Marked items have an increased number of contacts while following DIN standards.

XC5B Double-row Sockets, DIN B-type (Standard)


■ Dimensions (unit: mm)

XC5B-□□21 (With straight DIP terminals)




XC5B
DIP terminal cross-section view





Mounting holes (bottom view)




Dimensions

No. of		Dime	ensions (Coding Key slot		
contacts	Α	В	С	D	Е	positions (contact No.)
20	38.9	29.1	22.86	34.12	27.1	3, 8
32	54.2	44.4	38.10	49.36	42.3	5, 12
44	69.4	59.6	53.34	64.60	57.5	4, 9, 14, 19
50	77.0	67.2	60.96	72.22	65.2	5, 10, 16, 21
64	94.8	85.0	78.74	90.00	82.9	6, 13, 20, 27
100	140.5	130.7	124.46	135.72	128.7	10, 20, 31, 41

No. of	Straight DIP terminals
contacts	Model
20*	XC5B-2021
32	XC5B-3221
44*	XC5B-4421
50*	XC5B-5021
64	XC5B-6421
100*	XC5B-0121

^{*}Marked items have an increased number of contacts while following DIN standards.

XC5E Double-row Plugs, DIN Q-type (Reverse)



Dimensions

No. of			Coding Key positions				
contacts	Α	В	С	D	E	F	(contact No.)
20	38.9	32.1	22.86	34.12	28.1	29.3	3, 8
32	54.2	47.4	38.10	49.36	43.3	44.6	5, 12
44	69.4	62.6	53.34	64.60	58.5	59.8	4, 9, 14, 19
50	77.0	70.2	60.96	72.22	66.2	67.4	5, 10, 16, 21
64	94.8	88.0	78.74	90.00	83.9	85.2	6, 13, 20, 27
100	140.5	133.7	124.46	135.72	129.7	130.9	10, 20, 31, 41


No. of	Straight DIP terminals
contacts	Model
20*	XC5E-2021
32	XC5E-3221
44*	XC5E-4421
50*	XC5E-5021
64	XC5E-6421
100*	XC5E-0121

^{*}Marked items have an increased number of contacts while following DIN standards.


XC5F Double-row Sockets, DIN Q-type (Reverse)

■ Dimensions (unit: mm)

XC5F-□□22 (With right-angle DIP terminals)



Coding Key slot








XC5F DIP terminal cross-section view

Mounting holes (bottom view)



Dimensions


No. of		Dime	Coding Key slot			
contacts	Α	В	С	D	E	positions (contact No.)
20	37.9	29.1	22.86	33.02	27.1	3, 8
32	53.2	44.4	38.10	48.26	42.3	5, 12
44	68.4	59.6	53.34	63.50	57.5	4, 9, 14, 19
50	76.0	67.2	60.96	71.12	65.2	5, 10, 16, 21
64	93.8	85.0	78.74	88.90	82.9	6, 13, 20, 27
100	139.5	130.7	124.46	134.62	128.7	10, 20, 31, 41

No. of contacts	Terminal type	Model		
20*		XC5F-2022		
32		XC5F-3222		
44*	Right-angle DIP terminals	XC5F-4422		
50*		XC5F-5022		
64		XC5F-6422		
100*		XC5F-0122		

^{*}Marked items have an increased number of contacts while following DIN standards.

XC5C Triple-row Plugs, DIN C-type (Standard)





Dimensions

No. of			Coding Key positions					
contacts	Α	В	С	D	Е	F	(contact No.)	
32*	53.2	47.4	38.10	48.26	43.3	44.6	5, 12	
48	53.2	47.4	38.10	48.26	43.3	44.6	5, 12	
64*	93.8	88.0	78.74	88.90	83.9	85.2	6, 13, 20, 27	
96	93.8	88.0	78.74	88.90	83.9	85.2	6, 13, 20, 27	

^{*}Has no center row (row b).

No. of contacts	Terminal type	Model
32*		XC5C-3222
48	Right-angle DIP	XC5C-4822
64*	terminals	XC5C-6422
96		XC5C-9622

^{*}Has no center row (row b).

XC5D Triple-row Sockets, DIN C-type (Standard)

XC5D-□21 (With straight DIP terminals) XC5D DIP terminal cross-section view Mounting holes (bottom view)

Dimensions

No. of contacts		Dim	Coding Key slot			
	Α	В	С	D	E	positions (contact No.)
32*	54.2	44.4	38.10	49.36	42.3	5, 12
48	54.2	44.4	38.10	49.36	42.3	5, 12
64*	94.8	85.0	78.74	90.00	82.9	6, 13, 20, 27
96	94.8	85.0	78.74	90.00	82.9	6, 13, 20, 27

0.8 +0.1 dia. (DIP terminals)

■Ordering Information

No. of	Straight DIP terminals				
contacts	Model				
32*	XC5D-3221				
48	XC5D-4821				
64*	XC5D-6421				
96	XC5D-9621				

^{*}Has no center row (row b).

Two, 2.8 dia.


^{*}Has no center row (row b).

Two, 2.8 dia.

XC5G Triple-row Plugs, DIN R-type (Reverse)

■ Dimensions (unit: mm)

XC5G-□□21 (With straight DIP terminals)



0.8 +0.1 dia. (DIP terminals)

Dimensions

No. of			Coding Key positions				
contacts	Α	В	С	D	E	F	(contact No.)
48	54.2	47.4	38.10	49.36	43.3	44.6	5, 12
64*	94.8	88.0	78.74	90.00	83.9	85.2	6, 13, 20, 27
96	94.8	88.0	78.74	90.00	83.9	85.2	6, 13, 20, 27


^{*}Has no center row (row b).

No. of	Straight DIP terminals		
contacts	Model		
48	XC5G-4821		
64*	XC5G-6421		
96	XC5G-9621		

^{*}Has no center row (row b).

XC5H Triple-row Sockets, DIN R-type (Reverse)


■ Dimensions (unit: mm)



XC5H DIP terminal cross-section view

Mounting holes (bottom view)





Dimensions

No. of		Dime	Coding Key slot			
contacts	Α	В	С	D	Е	positions (contact No.)
48	53.2	44.4	38.10	48.26	42.3	5, 12
64*	93.8	85.0	78.74	88.90	82.9	6, 13, 20, 27
96	93.8	85.0	78.74	88.90	82.9	6, 13, 20, 27


^{*}Has no center row (row b).


No. of contacts	Terminal type	Model	
48	Dight angle DID	XC5H-4822	
64*	Right-angle DIP terminals	XC5H-6422	
96		XC5H-9622	

^{*}Has no center row (row b).

■ Tools and Accessories (Sold Separately)


Coding Cutter XY2D-0001






- 1. Cut the Coding Key(s) in the slot in the plug housing wall with the special cutting tool (XY2D-0001).
- Note: Coding Cutters may not work with some DIN-style connector combinations. In that case, contact your OMRON representative.

Coding Key XC5Z-0001



Material: PBT resin (UL94HB)/white

Model XC5Z-0001



- 2. Insert the special Coding Key (XC5Z-0001) into the Coding Key slots in the housing wall of the corresponding
- Note: 1. Each XC5Z-0001 has four Coding Keys.
 - 2. Coding Keys may not work with some DIN-style connector combinations. In that case, contact your OMRON representative.


Temporary Fastening Pins XC5Z-0002

(For use with 1.6-mm boards)



Material: stainless steel

Model XC5Z-0002




Fastening pins (XC5Z-0002) are used to keep the connector flush against the board during automated soldering.

- Note: 1. For the XC5A, XC5F, XC5C, and XC5H.
 - 2. Temporary fastening pins can-not be used with DIN-style connectors.

Dust Cover XC5T-962

(For DIN41612 C- or R-type Triple-row Plugs with 64 or 96 contacts)

(For DIN41612 C- or R-type Triple-row Sockets with 64 or 96 contacts)




Material: Polyamide resin (UL94 V-2)/natural


This is a dust-proof cover that is not used at the moment and not the one that protects against flux in automatic soldering.

■Mating Diagrams

(unit: mm)



Note: By combining a Standard and a Reverse Connector, stacking and horizontal connections can be made. In this case, the triangular marks (terminal number 1) on the Plug and the Socket will not match.




■Precautions **Correct Use**

Soldering

Automated Soldering

Use masking tape to mask Right-angle Connectors before automated soldering.




(Recommended tape: 3M Sumitomo #214)

Automated Soldering Conditions (Jet Flow)

- 1. Soldering temperature: 250±5°C
- 2. Continuous soldering time: Within 5±1 s

Basic Mating Dimensions

Mating dimensions for all Connectors should be as shown in the following diagram.



 α : 3.55 mm

The distance between the center line of the mounting holes on the mother board and the daughter board. (This center line is shifted 0.3 mm toward row a from row b.) β: 2.54 mm

The distance between the mounting holes on the daughter board and row a.


γ: 5.3 mm


The distance between the edge of the daughter board and row a.

 δ : 12.4 to 14.2 mm

To ensure reliability, be sure to keep the Connectors within these dimensions when mounting.

The allowable margins for mating the Connectors are shown below.





■Approval Standard

The approval rating values for overseas standards are different from the performance values determined individually. Confirm the values before use.

Model	Standard	File No.	Rating
XC5A-□□22	UL certified product (Recognized)	E103202	300 V, 2 A
	CSA certified product (Certified)	LR 62678	
XC5B-□□21	UL certified product (Recognized)	E103202	300 V, 2 A
	CSA certified product (Certified)	LR 62678	
XC5E-□□21	UL certified product (Recognized)	E103202	300 V, 2 A
	CSA certified product (Certified)	LR 62678	
XC5F-□□22	UL certified product (Recognized)	E103202	300 V, 2 A
	CSA certified product (Certified)	LR 62678	
XC5C-□□22	UL certified product (Recognized)	E103202	300 V, 2 A
	CSA certified product (Certified)	LR 62678	
XC5D-□□21	UL certified product (Recognized)	E103202	300 V, 2 A
	CSA certified product (Certified)	LR 62678	
XC5G-□□21	UL certified product (Recognized)	E103202	300 V, 2 A
	CSA certified product (Certified)	LR 62678	
XC5H-□□22	UL certified product (Recognized)	E103202	300 V, 2 A
	CSA certified product (Certified)	LR 62678	
Y2D-0001 Non Approved Models			
XC5Z-0001	Non Approved Models		
XC5Z-0002	Non Approved Models		
XC5T-962	Non Approved Models		
XC5T-963	Non Approved Models		

13



Please check each region's Terms & Conditions by region website.

OMRON Corporation

Device & Module Solutions Company

Regional Contact

Americas

https://components.omron.com/us

Asia-Pacific

https://components.omron.com/ap

Korea

https://components.omron.com/kr

Europe

https://components.omron.com/eu

China

https://components.omron.com.cn

Japan

https://components.omron.com/jp

© OMRON Corporation 2012-2024 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

Cat. No. G049-E1-06

0424 (0412)