


Actuator Mounted Connector Models

- Snap-in mounted (Compatible thickness: $t = 1, 1.2, 1.6$ mm)
- Compatible connector: CT connector manufactured by TE Connectivity



Be sure to read *Safety Precautions* on Page 3.

RoHS Compliant

Ordering Information

Photomicrosensor

Appearance	Sensing method	Connecting method	Sensing distance	Aperture size (H × W) (mm)	Output type	Model	Minimum packing unit (Unit: pcs)
	Actuator	Connector	3.6 mm (Slot width)	Both emitting side and detecting side 2.4 × 0.5	Phototransistor	EE-SA107-P2	1

Note: Order in multiples of minimum packing unit.

Ratings, Characteristics and Exterior Specifications

Absolute Maximum Ratings (Ta = 25°C)

Item	Symbol	Rated value	Unit
Emitter			
Forward current	I_F	50*	mA
Pulse forward current	I_{FP}	—	A
Reverse voltage	V_R	4	V
Detector			
Collector-Emitter voltage	V_{CEO}	30	V
Emitter-Collector voltage	V_{ECO}	5	V
Collector current	I_C	20	mA
Collector dissipation	P_C	100*	mW
Operating temperature	T_{opr}	-25 to 85	°C
Storage temperature	T_{stg}	-40 to 85	°C
Soldering temperature	T_{sol}	—	°C

* Refer to the temperature rating chart if the ambient temperature exceeds 25°C.

Exterior Specifications

Connecting method	Weight (g)	Material	
		Case	Transparent cover
Connector	1.6	Polycarbonate	Polycarbonate

Electrical and Optical Characteristics (Ta = 25°C)

Item	Symbol	Value			Unit	Condition	
		MIN.	TYP.	MAX.			
Emitter							
	Forward voltage	V _F	—	1.2	1.5	V	I _F = 30 mA
	Reverse current	I _R	—	0.01	10	μA	V _R = 4 V
	Peak emission wavelength	λ _P	—	940	—	nm	I _F = 30 mA
Detector							
	Light current	I _L	0.5	—	14	mA	I _F = 20 mA, V _{CE} = 5 V
	Dark current	I _D	—	—	200	nA	V _{CE} = 10 V, 0 lx
	Leakage current	I _{LEAK}	—	—	—	μA	—
	Collector-Emitter saturated voltage	V _{CE} (sat)	—	0.1	0.4	V	I _F = 20 mA, I _L = 0.3 mA
	Peak spectral sensitivity wavelength	λ _P	—	850	—	nm	V _{CE} = 5 V
Rising time		t _r	—	8	—	μs	V _{CC} = 5 V, R _L = 100 Ω, I _L = 1 mA
Falling time		t _f	—	8	—	μs	V _{CC} = 5 V, R _L = 100 Ω, I _L = 1 mA

Engineering Data (Reference Value)

Fig 1. Forward Current vs. Collector Dissipation Temperature Rating




Fig 2. Forward Current vs. Forward Voltage Characteristics (Typical)




Fig 3. Light Current vs. Forward Current Characteristics (Typical)




Fig 4. Light Current vs. Collector-Emitter Voltage Characteristics (Typical)




Fig 5. Relative Light Current vs. Ambient Temperature Characteristics (Typical)




Fig 6. Dark Current vs. Ambient Temperature Characteristics (Typical)




Fig 7. Response Time vs. Load Resistance Characteristics (Typical)




Fig 8. Sensing Position Characteristics (Typical)




Fig 9. Sensing Position Characteristics (Typical)






Fig 10. Response Time Measurement Circuit



Recommended Mounting Holes: Refer to EE-SA407-P2. Reference Actuator Design Drawing



- Note:**
1. Make sure that the portions marked with dotted lines have no burrs.
 2. The material of the actuator must be selected by considering the infrared permeability of the actuator.

Safety Precautions

To ensure safe operation, be sure to read and follow the Instruction Manual provided with the Sensor.

CAUTION

This product is not designed or rated for ensuring safety of persons either directly or indirectly.
Do not use it for such purposes.



Precautions for Correct Use

Do not use the product in atmospheres or environments that exceed product ratings.

Precautions for Safe Use

Do not use the product with a voltage or current that exceeds the rated range.

Applying a voltage or current that is higher than the rated range may result in explosion or fire.

Do not miswire such as the polarity of the power supply voltage.

Otherwise the product may be damaged or it may burn.


This product does not resist water. Do not use the product in places where water or oil may be sprayed onto the product.

Dimensions and Internal Circuit

(Unit: mm)


Photomicrosensor

EE-SA107-P2



Aperture size (H x W)


Emitter	Detector
2.4 x 0.5	2.4 x 0.5



* The asterisked dimension is specified by datum A only.

Recommended compatible connector: Connector manufactured by TE Connectivity 179228-3 (crimp type)
173977-3 (insulation displacement crimp type)
175778-3 (crimp type)

Internal circuit



Terminal No.	Name
A	Anode
C	Collector
K, E	Cathode, Emitter

Unless otherwise specified, the tolerances are as shown below.

Dimensions	Tolerance
3 mm max.	±0.3
3 < mm ≤ 6	±0.375
6 < mm ≤ 10	±0.45
10 < mm ≤ 18	±0.55
18 < mm ≤ 30	±0.65

Please check each region's Terms & Conditions by region website.

OMRON Corporation

Electronic and Mechanical Components Company

Regional Contact

Americas

<https://www.components.omron.com/>

Asia-Pacific

<https://ecb.omron.com.sg/>

Korea

<https://www.omron-ecb.co.kr/>

Europe

<http://components.omron.eu/>

China

<https://www.ecb.omron.com.cn/>

Japan

<https://www.omron.co.jp/ecb/>